


Fixture Lengths

CSS-R | RAS


Fixture Type

Approval

Continuous Run Individual Cable/Arm Centers



Stand Alone Cable/Arm Centers & Overall Length




Fixture Length	Cable/Arm Centers (in)	Fixture Length	Cable/Arm Centers (in)	Fixture Length	Cable/Arm Centers (in)	Fixture Length	Cable/Arm Centers (in)	Overall Length (in)
2'	26.000"	2'	26.000"	2'	26.000"	2'	26.000"	27.125"
3'	38.000"	3'	38.000"	3'	38.000"	3'	38.000"	39.125"
4'	50.000"	4'	50.000"	4'	50.000"	4'	50.000"	51.125"
5'	62.000"	5'	62.000"	5'	62.000"	5'	62.000"	63.125"
6'	74.000"	6'	74.000"	6'	74.000"	6'	74.000"	75.125"
7'	86.063"	7'	86.063"	7'	86.063"	7'	86.063"	87.188"
8'	98.063"	8'	98.063"	8'	98.063"	8'	98.063"	99.188"

Continuous Run Lengths and Fixture Length Segments

9	9' - 5.125"	6-3	23	22' - 7.250"	8-8-6	37	36' - 11.375"	8-8-8-8-4
10	10' - 5.188"	8-2	24	23' - 7.313"	8-8-7	38	37' - 11.375"	8-8-8-8-5
11	11' - 5.188"	8-3	25	24' - 7.313"	8-8-8	39	38' - 11.375"	8-8-8-8-6
12	12' - 5.188"	6-6	26	25' - 9.250"	8-8-6-3	40	39' - 11.438"	8-8-8-8-7
13	13' - 5.188"	8-5	27	26' - 9.313"	8-8-8-2	41	40' - 11.438"	8-8-8-8-8
14	14' - 5.188"	8-6	28	27' - 9.313"	8-8-8-3	42	42' - 1.375"	8-8-8-8-6-3
15	15' - 5.25"	8-7	29	28' - 9.313"	8-8-8-4	43	43' - 1.438"	8-8-8-8-8-2
16	16' - 5.25"	8-8	30	29' - 9.313"	8-8-8-5	44	44' - 1.438"	8-8-8-8-8-3
17**			31	30' - 9.313"	8-8-8-6	45	45' - 1.438"	8-8-8-8-8-4
18	17' - 7.250"	8-7-2	32	31' - 9.375"	8-8-8-7	46	46' - 1.438"	8-8-8-8-8-5
19	18' - 7.250"	6-6-6	33	32' - 9.375"	8-8-8-8	47	47' - 1.438"	8-8-8-8-8-6
20	19' - 7.250"	8-8-3	34	33' - 11.313"	8-8-8-6-3	48	48' - 1.500"	8-8-8-8-8-7
21	20' - 7.250"	8-8-4	35	34' - 11.375"	8-8-8-8-2	49	49' - 1.500"	8-8-8-8-8-8
22	21' - 7.250"	8-8-5	36	35' - 11.375"	8-8-8-8-3	50	50' - 3.438"	8-8-8-8-8-6-3

** Skips length to get closer to nominal length



#825-00002
V-0917